

DAAMS Tubes and Preconcentrator Tubes (PCTs)

The predecessor to the US Chemical Materials Agency developed thermal desorption tube monitoring methods for chemical warfare agents to be implemented at US sites associated with CW materials. That method became known as The Depot Area Air Monitoring System (DAAMS). The method has been in use for over 20 years now. Camasco has been a leader in the development of quality standards and innovations for DAAMS since 1991.

DAAMS & PCTs

DAAMS tubes are used for historical monitoring and surveillance at worldwide military chemical weapons storage sites, research laboratories and NATO military theaters. PCTs are used in ACAMS and CMS Minicams for near real-time monitoring of chemical warfare agents.

All DAAMS tubes and PCTs are pressure drop tested to ensure proper flow rates. All sorbents are preconditioned. Certificates of Compliance are provided to address site specific requirements.

Camasco provides many options, including our patented ceramic barcode, high temperature barcode labels, laser bonded color ceramic appliques and color ceramic bands and dots facilitating lot identification and simplifying LIMS management. Additionally, we offer centerless grinding, ground ends, chamfers, lapping, annealing, polishing and fire-polishing.

6mm DAAMS



8mm DAAMS



3mm DAAMS Transfer Tubes



3mm Preconcentrator Tubes



4mm Preconcentrator Tubes



3mm Preconcentrator Tubes for CMS Minicams



6mm DAAMS Tubes	Part Number
Chromosorb 106 60/80 mesh	60403
Tenax TA 60/80 mesh	60420
Tenax GR 60/80 mesh	60420GR
3mm DAAMS Transfer Tubes	
Chromosorb 106 60/80 mesh	30403
Tenax TA 60/80 mesh	30420
Tenax GR 60/80 mesh	30420GR
HayeSep D/Tenax TA	30408-20
Chromosorb 106/Tenax GR	30419
HayeSep D 40/60 mesh	41608
8mm DAAMS Tubes	
Chromosorb 106 60/80 mesh	80403
Tenax TA 60/80 mesh	80420
Tenax GR 60/80 mesh	80420GR

8mm DAAMS Tubes Dynatherm	Part Number
Chromosorb 106 60/80 mesh	A80403
Tenax TA 60/80 mesh	A80420
Tenax GR 60/80 mesh	A80420GR
3mm Preconcentrator Tubes	
HayeSep D 40/60 mesh	31608
Tenax TA 35/60 mesh	31620
Tenax GR 35/60 mesh	31620GR
4mm Preconcentrator Tubes	
Tenax TA 35/60 mesh	41620
Tenax GR 35/60 mesh	41620GR
3mm Minicams PCTs	
HayeSep D 40/60 mesh	M31608
Tenax TA 35/60 mesh	M31620
Tenax GR 35/60 mesh	M31620GR

To talk to an expert, or for a free sample, call 800-448-3280.